

# Technical data sheet

## Product features



### INFINITY multifunctional device 15x GN 1/1, wheels

|                       |                                  |                                |
|-----------------------|----------------------------------|--------------------------------|
| <b>Model</b>          | <b>SAP Code</b>                  | 00038859                       |
| INFINITY 1511 KL LD N | <b>A group of articles - web</b> | Šokery a multifunkční zařízení |



- Shock cooling cycle kg / min (+3 ° C): 70/86
- Shock freeze cycle kg / min (-18 ° C): 30/182
- Minimum device temperature [°C]: -40
- Maximum device temperature [°C]: 85
- Probe: 4-points
- Insulation thickness [mm]: 60
- Control type: Touchscreen
- Display size: 9"
- User programmable cycles: Yes, with save options
- Defrosting cycle: Yes
- Proving cycle: Yes

|                            |                    |                                              |             |
|----------------------------|--------------------|----------------------------------------------|-------------|
| <b>SAP Code</b>            | 00038859           | <b>Number of GN / EN</b>                     | 15          |
| <b>Net Width [mm]</b>      | 790                | <b>GN / EN size in device</b>                | GN 1/1      |
| <b>Net Depth [mm]</b>      | 839                | <b>GN device depth</b>                       | 65          |
| <b>Net Height [mm]</b>     | 1990               | <b>Shock cooling cycle kg / min (+3 ° C)</b> | 70/86       |
| <b>Net Weight [kg]</b>     | 211.00             | <b>Shock freeze cycle kg / min (-18 ° C)</b> | 30/182      |
| <b>Power electric [kW]</b> | 2.772              | <b>Control type</b>                          | Touchscreen |
| <b>Loading</b>             | 400 V / 3N - 50 Hz | <b>Humidification</b>                        | Yes         |


# Technical data sheet

Technical drawing



## INFINITY multifunctional device 15x GN 1/1, wheels

|                       |                                  |                                |
|-----------------------|----------------------------------|--------------------------------|
| <b>Model</b>          | <b>SAP Code</b>                  | 00038859                       |
| INFINITY 1511 KL LD N | <b>A group of articles - web</b> | Šokery a multifunkční zařízení |



# Technical data sheet

## Product benefits



### INFINITY multifunctional device 15x GN 1/1, wheels

|                       |                                  |                                |
|-----------------------|----------------------------------|--------------------------------|
| <b>Model</b>          | <b>SAP Code</b>                  | 00038859                       |
| INFINITY 1511 KL LD N | <b>A group of articles - web</b> | Šokery a multifunkční zařízení |

1

#### 6v1

dokáže zastoupit 6 zařízení (lednice, mrazák, šoker, hodbox, kynárna, trouba)

- díky obrovské variabilitě šetří místo, čas, energii a náklady na pořízení dalších zařízení

2

#### Nerezové tělo i vnitřek

odolnost  
hygiena

- díky celonerezové konstrukci se velmi snadno udržuje a tím šetří náklady

3

#### Sledování parametrů HACCP

snadná evidence všech potřebných parametrů

- bezproblémové dokazování správného nakládání s potravinami při případné kontrole

4

#### Přednastavené cykly

velmi jednoduché a intuitivní ovládání

- obsluhu může zvládnout i méně kvalifikovaná obsluha

5

#### Pomalé vaření

lepší chuť  
menší hmotnostní ztráty při vaření

- díky menším ztrátám hmotnosti zařízení šetří náklady

6

#### Vícebodová sonda

precizní sledování teploty chlazení/mražení/vaření

- díky sondě je lépe zajištěna bezpečnost potravin
- vzhledem k ukončení zchlazování/zmrazování/vaření po dosažení teploty šetří energii a čas

7

#### Rozmrazení

připravenost zamražené potravin na zpracování na čas

- úspora času
- řízená manipulace s potravinami

8

#### Vaření přes noc

možnost přednastavit celé cykly programů a spustit přes noc bez obsluhy

- úspora kapacity zařízení přes den
- úspora lidské kapacity a času, díky bezobslužnému provozu zařízení přes noc

# Technical data sheet

## Technical parameters



### INFINITY multifunctional device 15x GN 1/1, wheels

|                       |                                  |                                |
|-----------------------|----------------------------------|--------------------------------|
| <b>Model</b>          | <b>SAP Code</b>                  | 00038859                       |
| INFINITY 1511 KL LD N | <b>A group of articles - web</b> | Šokery a multifunkční zařízení |

**1. SAP Code:**

00038859

**2. Net Width [mm]:**

790

**3. Net Depth [mm]:**

839

**4. Net Height [mm]:**

1990

**5. Net Weight [kg]:**

211.00

**6. Gross Width [mm]:**

830

**7. Gross depth [mm]:**

860

**8. Gross Height [mm]:**

2120

**9. Gross Weight [kg]:**

233.00

**10. Device type:**

Electric unit

**11. Material:**

AISI 304

**12. Exterior color of the device:**

Stainless steel

**13. Opening of device:**

Hinges on the left

**14. Power electric [kW]:**

2.772

**15. Loading:**

400 V / 3N - 50 Hz

**16. Control type:**

Touchscreen

**17. Display size:**

9"

**18. Refrigerant:**

R290

**19. Number of GN / EN:**

15

**20. GN / EN size in device:**

GN 1/1

**21. GN device depth:**

65

**22. Minimum device temperature [°C]:**

-40

**23. Maximum device temperature [°C]:**

85

**24. Shock freeze cycle kg / min (-18 ° C):**

30/182

**25. Shock cooling cycle kg / min (+3 ° C):**

70/86

**26. Insulation thickness [mm]:**

60

**27. Long-term cooling function:**

Yes

**28. Longterm freezing function:**

Yes

# Technical data sheet

Technical parameters



## INFINITY multifunctional device 15x GN 1/1, wheels

|                       |                                  |                                |
|-----------------------|----------------------------------|--------------------------------|
| <b>Model</b>          | <b>SAP Code</b>                  | 00038859                       |
| INFINITY 1511 KL LD N | <b>A group of articles - web</b> | Šokery a multifunkční zařízení |

**29. Probe:**

4-points

**30. Self-diagnostics:**

Yes

**31. Interior lighting:**

Yes

**32. HACCP:**

Yes

**33. Low temperature heat treatment:**

Yes

**34. Low temperature cooking span [°C]:**

52-85

**35. Defrosting cycle:**

Yes

**36. Proving cycle:**

Yes

**37. Adjustable feet:**

Yes

**38. User programmable cycles:**

Yes, with save options

**39. USB port:**

Yes, for HACCP and firmware update

**40. Castors:**

Yes

**41. Real time monitoring parameters:**

Energy consumption, Chamber temperature, Probe temperature, Graph with the course of temperature and consumption

**42. Drain connection:**

Yes

**43. Cross-section of conductors CU [mm²]:**

0,5

**44. Humidification:**

Yes